



K I N T E K P R E S S

C o n t a c t u s f o r m o r e c a t a l o g s o f

KINTEK PRESS

> > >

KINTEK

Press



C i p

: P C I M



KINTEK Lab Manual Isostatic Press

	PCI M- 12T	PCI M- 20T	PCI M- 40T	PCI M- 60T
	0 - 12 T (0 - 17 MP a)	0 - 20 T (0 - 21 MP a)	0 - 40 T (0 - 30 MP a)	0 - 60 T (0 - 34 MP a)
	95 mm (d)	110 mm (d)	130 mm (d)	150 mm (d)
T	40 mm	40 mm	50 mm	50 mm
	10 - 40	10 - 40	10 - 40	10 - 40
	0 - 300 MP a			
	22 × 70 mm (M × N)	30 × 120 mm (M × N)	40 × 150 mm (M × N)	50 × 150 mm (M × N)
	305 × 195 × 530 mm (L × W × H)	305 × 195 × 600 mm (L × W × H)	355 × 215 × 710 mm (L × W × H)	405 × 240 × 720 mm (L × W × H)
	90 Kg	100 Kg	130 Kg	180 Kg

1 . 7	1 . 86 [MP a	25 [MP a
3 . 5	3 . 72 [MP a	50 MP a
5	5 . 57 [MP a	75 [MP a
7	7 . 43 MP a	100 [MP a
8 . 7	9 . 29 MP a	125 [MP a
10 . 5	11 . 2 [MP a	150 [MP a
14	14 . 8 MP a	200 MP a
17 . 5	18 . 6 MP a	250 MP a

2 1	2 2 . 3 [MP a	3 0 0 [MP a
	3 5 MP a	

C i p

: P C I E



K I N T E K

	P C I E - 1 2 T	P C I E - 2 0 T	P C I E - 4 0 T	P C I E - 6 0 T
	0 - 1 2 T (0 - 1 7 M P a)	0 - 2 0 T (0 - 2 1 M P a)	0 - 4 0 T (0 - 3 0 M P a)	0 - 6 0 T (0 - 3 4 M P a)
	9 5 m m (d)	1 1 0 m m (d)	1 3 0 m m (d)	1 5 0 m m (d)
	0 . 0 - 4 0 . 0 M P a	0 . 0 - 4 0 . 0 M P a	0 . 0 - 4 0 . 0 M P a	0 . 0 - 4 0 . 0 M P a
(T)	4 0 m m	4 0 m m	5 0 m m	5 0 m m
	/	/	/	/
	/	/		
	1 0 - 4 0	1 0 - 4 0	1 0 - 4 0	1 0 - 4 0
	0 - 3 0 0 M P a	0 - 3 0 0 M P a	0 - 3 0 0 M P a	0 - 3 0 0 M P a
	2 2 × 7 0 m m (M × N)	3 0 × 1 2 0 m m (M × N)	4 0 × 1 5 0 m m (M × N)	5 0 × 1 5 0 m m (M × N)
	3 0 5 × 4 3 0 × 5 3 0 m m (L × W × H)	3 0 5 × 4 3 0 × 6 0 0 m m (L × W × H)	3 5 5 × 4 5 0 × 7 1 0 m m (L × W × H)	4 0 5 × 4 7 0 × 7 2 0 m m (L × W × H)
	5 5 0 W (2 2 0 V / 1 1 0)	5 5 0 W (2 2 0 V / 1 1 0)	5 5 0 W (2 2 0 V / 1 1 0)	5 5 0 W (2 2 0 V / 1 1 0)
	1 1 0 K g	1 2 0 K g	1 5 0 K g	2 0 0 K g

C i p

: P C I A



(C I P)

K I N T E K

	PCI A - 20T	PCI A - 40T	PCI A - 60T	PCI A - 100T
	110 mm (d)	130 mm (d)	150 mm (d)	200 mm (d)
	-	-	-	-
	4.3 LCD	4.3 LCD	4.3 LCD	7 LCD
	300 - 500MPA	300 - 500MPA	300 - 500MPA	300 - 500MPA
	30 × 150mm(M×N)	40 × 150mm(M×N)	50 × 150mm/ 30 × 150mm	60 × 150(M×N)
(T)	50mm	50mm	50mm	50mm
	240 × 390 × 560 x x	280 × 460 × 660 x x	/	330 × 580 × 720 x x
	550W(220V / 110	550W(220V / 110	550W(220V / 110)	550W(220V / 110)
	120KG	180KG	240KG	290KG

C i p

: P C E S I



K I N T E K L a b

	PCESI - 65T	PCESI - 100T	PCESI - 150T	PCESI - 200T
	0 - 65T	0 - 100T	0 - 150T	0 - 200T
	160mm (d)	200mm (d)	200mm (d)	290mm (d)
	-	-	-	-
	7" LCD			
	0 - 300MPa	0 - 300MPa	0 - 300MPa	0 - 300MPa
	50 × 150mm(M×N)	60 × 150mm(M×N)	80 × 150mm(M×N)	90 × 150mm(M×N)
(T)	50mm	50mm	50mm	50mm
	220 × 400mm(M×N)	260 × 400mm(M×N)	280 × 400mm(M×N)	290 × 420mm(M×N)
	700 × 450 × 1050mm(L × W × H)	850 × 500 × 1100mm(L × W × H)	950 × 550 × 1150mm(L × W × H)	1000 × 650 × 1200mm(L × W × H)
	1500W 220V / 110V			
	350kg	580kg	680kg	980kg



K i n t e k P r e s s

W h a t s A p p
Image not found