



KINTEK PRESS

Contact us for more catalogs of

# KINTEK PRESS

> > >

KINTEK

Press



: P M I D



K I N T E K

X R F

F T I R

|  |  |                       |
|--|--|-----------------------|
|  |  | P M I D               |
|  |  |                       |
|  |  | H R C 6 8   H R C 8 5 |
|  |  | 1 3   m m ( M )       |
|  |  | 2 0 m m ( N )         |
|  |  | 4 3 * 7 8 m m   L * H |
|  |  | 0 . 7 6 K g           |
|  |  |                       |

: P M I



K I N T E K

-

|  | P M I - A                       | P M I - B                       |
|--|---------------------------------|---------------------------------|
|  | H R C 6 8   H R C 8 5           |                                 |
|  | 1 3   m m ( M )                 | 7   m m ( M )                   |
|  | 1 0 m m ( N )                   | 5 m m ( N )                     |
|  | 7 6 * 5 0 * 7 0 m m   L * W * H | 7 6 * 3 0 * 7 0 m m   L * W * H |
|  | 0 . 7 6 K g                     | 0 . 3 5 K g                     |
|  |                                 |                                 |

: PMN

CR 1 6 -

CR 3 0



|  |                                   |
|--|-----------------------------------|
|  | PMN                               |
|  | CR 1 6 , CR 2 0 , CR 2 4 , CR 3 0 |
|  | 0 . 8   1 . 2                     |
|  | CR 1 6   CR 2 0   CR 2 4   CR 3 0 |
|  |                                   |

: PCKM



K I N T E K

|  |                     |                     |
|--|---------------------|---------------------|
|  |                     |                     |
|  | CR16 CR20 CR24 CR30 | CR16 CR20 CR24 CR30 |
|  |                     | 0.8-1.2             |
|  | 60*140mm L*H        | 60X140mm LXH        |
|  | 1.85kg              | 1.85kg              |

: PMS - F



K I N T E K

|  |                                |
|--|--------------------------------|
|  | PMSY                           |
|  | Cr12MoV                        |
|  | HRC60 HRC62                    |
|  | 12*12 15*15 18*18 20*20 mm (M) |
|  | 40mm (N)                       |
|  | 88*175mm L*H                   |
|  | 3.0Kg                          |
|  |                                |

: PMSY



Cr 12Mo V

|  |                        |
|--|------------------------|
|  | PMSY                   |
|  | Cr 12Mo V              |
|  | HRC60 HRC62            |
|  | 12 13 15 18 20mm ( M ) |
|  | 40mm ( N )             |
|  | 88 * 175mm L * H       |
|  | 3 . 0 Kg               |
|  |                        |


: P C M C



K I N T E K

|  |                                                 |
|--|-------------------------------------------------|
|  | P C M C                                         |
|  | C r 1 2 M o V                                   |
|  | H R C 6 0   H R C 6 2                           |
|  | 1 0   1 2   1 3   1 5   1 8   2 0   m m   ( M ) |
|  | 1 0 0 m m   ( N )                               |
|  | 5 3 * 2 2 0 m m   L * H                         |
|  | 4 . 8 K g                                       |
|  |                                                 |

: P M L




o V

C r 1 2 M

|  |                                                   |
|--|---------------------------------------------------|
|  | P M T                                             |
|  | C r 1 2 M o V                                     |
|  | H R C 6 0   H R C 6 2                             |
|  | 6 m m   8 m m   1 0 m m   1 5 m m   2 0 m m   - M |
|  | 4 0 m m   -   N                                   |
|  | 9 8 * 1 2 0 m m   L * H                           |
|  | 5 K g                                             |
|  |                                                   |

: PMPD



|     |                                     |
|-----|-------------------------------------|
|     | PMPD                                |
|     | (                                   |
|     | Cr12MoV                             |
|     | HRC60 HRC62                         |
|     | 5x5, 10x10, 15x15, 20x20 mm (M) ( ) |
|     | 40mm (N) ( )                        |
| ( ) | 53*120mm L*H                        |
|     | 1.4Kg                               |
|     |                                     |

: P M O



3 - 8 0 mm

C r 1 2 M o V

|  |                       |         |                |                                         |
|--|-----------------------|---------|----------------|-----------------------------------------|
|  | P M Q                 |         |                |                                         |
|  | C r 1 2 M o V         |         |                |                                         |
|  | H R C 6 0 - H R C 6 2 |         |                |                                         |
|  | 7 - 3                 | 1 0 - 5 | 2 0 - 1 0 mm M | 3 0 - 1 0 5 0 - 2 0 mm D                |
|  | 4 0 mm                | N       |                | 4 5 mm D                                |
|  | 5 3 * 1 2 0 mm        | L * H   |                | 7 2 * 1 0 0 mm 8 8 * 1 2 0 mm ( D * L ) |
|  | 1 . 4 K g             |         |                | 3 . 5 k g 5 k g                         |
|  |                       |         |                |                                         |

: PMQ



/  
3 -  
80 mm K I N T E K

|  |              |   |    |    |          |               |    |    |        |  |
|--|--------------|---|----|----|----------|---------------|----|----|--------|--|
|  | PMQ          |   |    |    |          |               |    |    |        |  |
|  | Cr12MoV      |   |    |    |          |               |    |    |        |  |
|  | HRC60 HRC62  |   |    |    |          |               |    |    |        |  |
|  | 6            | 8 | 10 | 15 | 20mm (M) | 30            | 40 | 50 | mm (M) |  |
|  | 40mm (N)     |   |    |    |          | 60mm (N)      |    |    |        |  |
|  | 53*120mm L*H |   |    |    |          | 88*150 mm L*H |    |    |        |  |
|  | 1.4kg        |   |    |    |          | 5.8kg         |    |    |        |  |
|  |              |   |    |    |          |               |    |    |        |  |

: PMT



K I N T E K

|  |                                 |
|--|---------------------------------|
|  |                                 |
|  | C r 1 2 M o V                   |
|  | H R C 6 0   H R C 6 2           |
|  | 6   8   1 0   1 5   2 0 m m   M |
|  | 4 0 m m   ( N )   (   )         |
|  | 5 3 * 1 2 0 m m   L * H         |
|  | 1 . 4 K g                       |
|  |                                 |

F t i r

X r f    K b r

:    P M X P



X R F

|  |                                                 |
|--|-------------------------------------------------|
|  | P M X P                                         |
|  | 3 0 0                                           |
|  | 2 5 m m    ( d )                                |
|  | 1 5   2 5   5 0   1 0 0   2 5 0   5 0 0   m   6 |
|  | 2 0 0 * 6 0 m m    ( D * H )                    |
|  | 2 2 0 V / 3 0 0 W                               |
|  |                                                 |

F t i r

X r f   K b r

:   P M X S



X R F

X R

F

|  |                         |
|--|-------------------------|
|  | P M X S                 |
|  | C r 1 2 M o V           |
|  | H R C 6 0   H R C 6 2   |
|  | 3 2 m m   4 0 m m   M   |
|  | 4 5 m m   ( N )         |
|  | 7 3 * 1 3 3 m m   L * H |
|  | 3 . 2 K g               |
|  |                         |

X r f

: P M X B



X R F

X R F

|  |         |
|--|---------|
|  | P M X B |
|--|---------|

|  |              |
|--|--------------|
|  | C - 12 N o v |
|--|--------------|

H R C 6 0 - H R C 6 2

|  |                    |
|--|--------------------|
|  | 3 2 m m    4 0 m m |
|--|--------------------|

4 5 m m    ( N )

|   |                     |
|---|---------------------|
| x | 7 3 m m × 1 3 3 m m |
|---|---------------------|

3 . 2 K g

| [ M P a      | 5 0     | 1 0 0   | 2 0 0   | 3 0 0   | 4 0 0   | 6 0 0   | 8 0 0   | 1 0 0 0 | 1 2 0 0 | 1 5 0 0 |
|--------------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 3 2 m m    [ | 4 . 0 2 | 8 . 0 4 | 1 6     | 2 4 . 1 | 3 2 . 1 | 4 8 . 2 | 6 4 . 3 | 8 0 . 4 | 9 6 . 5 | 1 2 0   |
| 4 0 m m    [ | 6 . 2 8 | 1 2 . 5 | 2 5 . 1 | 3 7 . 6 | 5 0 . 2 | 7 5 . 3 | 1 0 0   | 1 2 5   | 1 5 0   | 1 8 8   |

1 0 0    8 0 0 M P a

1 5 0 0 M P a

: PMW



Y T 1 5

X

|        |                                                                   |           |           |  |  |  |  |  |
|--------|-------------------------------------------------------------------|-----------|-----------|--|--|--|--|--|
|        | PMW - A                                                           | PMW - B   | PMW - C   |  |  |  |  |  |
|        | Y T 1 5                                                           |           |           |  |  |  |  |  |
|        | HRC85 - HRC90                                                     |           |           |  |  |  |  |  |
|        | 3 / 4 / 5 / 6 / 8 / 10 12 / 13 / 15 / 18 / 20 22 / 25 / 28 / 30 n |           |           |  |  |  |  |  |
|        | 30 mm                                                             | 40 mm     | 45 mm     |  |  |  |  |  |
|        | 43×93 mm                                                          | 53×120 mm | 73×133 mm |  |  |  |  |  |
| ( Kg ) | 0 . 7 8                                                           | 1 . 8     | 3 . 8     |  |  |  |  |  |

: P M A S



K I N T E K   A s s e m b l e   L a b   P r e s s  
M o l d


|         | P M A S - A                                                                  | P M A S - B                              | P M A S - C            | P M A S - D                  | P M A S - E                                   |
|---------|------------------------------------------------------------------------------|------------------------------------------|------------------------|------------------------------|-----------------------------------------------|
|         | C r 12 M o V                                                                 |                                          |                        |                              |                                               |
|         | H R C 6 0 - H R C 6 2                                                        |                                          |                        |                              |                                               |
|         | 3 * 3   4 * 4   5 * 5   6 * 6   8 * 12 * 12   15 * 15   18 * 18   mm   ( M ) | 12 * 12   15 * 15   18 * 18   mm   ( M ) | 30 * 30   40 * 40   mm | 50 * 50   60 * 60   mm ( M ) | 70 * 70   80 * 80   mm   ( M )                |
|         | 30 mm   ( N )                                                                | 40 mm   ( N )                            | 50 mm   ( N )          | 55 mm   ( N )                | 60 mm   ( N )                                 |
|         | 53 * 120 mm   L * H                                                          | 73 * 133 mm   L * H                      | 95 * 133 mm   L * H )  | 115 * 127 * 150 mm   * H     | 153 * 180 * 180 mm   L * H )   200 * 180 mm ( |
| ( K g ) | 1 . 2 K g                                                                    | 3 . 6 K g                                | 7 K g   14 K g         | 20 K g   30 K g              | 40 K g   50 K g                               |

: PMAC



|      | PMAC - A         | PMAC - B         | PMAC - C                                           | PMAC - D  | PMAC - E  |
|------|------------------|------------------|----------------------------------------------------|-----------|-----------|
|      | Cr12MoV          |                  |                                                    |           |           |
|      | HRC60 - HRC62    |                  |                                                    |           |           |
|      | 3 4 5 6 8<br>(M) | 12 13 15 18<br>M | 30 40mm M                                          | 50 60mm M | 70 80mm M |
|      | 30mm (N)         | 40 mm (N)        | 50 mm (N)                                          | 55 mm (N) | 60 mm (N) |
|      | 43*93mm L*H      | 53*120mm L*H     | 73*133mm 95*115*150mm 127*153*180mm 180*180mm (*H) |           |           |
| (Kg) | 0.75Kg           | 1.2Kg            | 3.8Kg 6.3Kg                                        | 14Kg 20Kg | 30Kg 40Kg |

: P C H F



K I N T E K

|  |                             |
|--|-----------------------------|
|  | P C H F                     |
|  | 0 - 500                     |
|  | SUS304                      |
|  | 0.75mm 1.35mm 1.75mm 2.75mm |
|  | 80x80 180x180 200x200mm     |
|  | 0.4kg 0.8kg 1.0kg           |
|  |                             |


: PMC



X

|                                        |                                   |  | PMC - A                                                                                          | PMC - B         | PMC - C          | PMC - D          | PMC - E                                      |
|----------------------------------------|-----------------------------------|--|--------------------------------------------------------------------------------------------------|-----------------|------------------|------------------|----------------------------------------------|
| PMC - F                                | PMC - G                           |  |                                                                                                  |                 |                  |                  |                                              |
| ASSAB +17                              | Cr12MoV                           |  |                                                                                                  |                 |                  |                  |                                              |
| HRC68 - HRC7                           | HRC60 - HRC62                     |  | 3 4 7 8 9 10 15 16 28 30 50 60 70<br>5 6 11.5 12 20 22 32 35<br>mm (M) 13 mm (M) 25mm M mm M m M |                 |                  |                  |                                              |
| 80 90 1<br>mm M                        | 120 150 (M)                       |  | 20mm ( 30mm (N)                                                                                  | 40mm (N)        | 45mm (N)         | 55 60 65mm (N )  |                                              |
| 65mm (N)                               | 65mm (N)                          |  | 43 * 78mm L * H                                                                                  | 43 * 93mm L * H | 53 * 120mm L * H | 73 * 133mm L * H | 88 * 150mm 9 8 * 180mm 108 * 180mm ( L * H ) |
| 118 * 150mm 8 * 180mm 1 80mm ( L * H ) | 168 * 180mm 218 * 180mm ( L * H ) |  | 0.55 Kg                                                                                          | 0.67 Kg         | 1.34 Kg          | 2.9 Kg           | 5.1Kg 7.3Kg 9Kg                              |
| 11.5 Kg 14 Kg 20 Kg 30 Kg 40 Kg        |                                   |  |                                                                                                  |                 |                  |                  |                                              |

: PMS



K I N T E K

Cr 12 M

o V

|        | PMS - A                               | PMS - B                               | PMS - C                        | PMS - D                        | PMS - E                             | PMS - F        | PMS - G         |
|--------|---------------------------------------|---------------------------------------|--------------------------------|--------------------------------|-------------------------------------|----------------|-----------------|
|        | Cr 12 Mo V                            |                                       |                                |                                |                                     |                |                 |
|        | HRC 60 - HRC 62                       |                                       |                                |                                |                                     |                |                 |
|        | 3 × 3 / 4 × 4 / 5 × 5<br>/ 10 × 10 mm | 12 × 12 / 15 × 15 / 1<br>/ 20 × 20 mm | 22 × 22 / 25 ×<br>/ 30 × 30 mm | 32 × 32 / 35 ×<br>/ 40 × 40 mm | 50 × 50 / 60 × 60 / 70<br>mm        | 81 - 150<br>mm | 151 -<br>200 mm |
|        | 20 mm                                 | 30 mm                                 | 40 mm                          | 45 mm                          | 55 / 60 / 65 mm                     | 60 mm          | 60 mm           |
|        | 43 × 93 mm                            | 53 × 120 mm                           | 73 × 133 mm                    | 88 × 150 mm                    | 98 × 150 mm / 118 ×<br>138 × 180 mm | 160 × 140      | 220 × 160 mm    |
| ( Kg ) | 0 . 65                                | 1 . 2                                 | 2 . 4                          | 4 . 8                          | 7 . 3 / 11 . 4 / 20                 | 25 kg - 40     | 45 kg - 80 kg   |

: P I P M



K I N T E K

: PMD



|   |                       |
|---|-----------------------|
|   | PMD                   |
|   | 300 500               |
|   | Cr12MoV               |
|   | HRC60 HRC62           |
|   | 0.02 - 0.1mm (N)      |
| 1 | 180*180*130mm * *     |
| 2 | 200*200*130mm (L*W*H) |
| 3 | 300*300*130mm (L*W*H) |
|   | 32Kg / 38Kg / 88Kg    |

: P M H



K I N T E K  
5 0 0

|  |                                             |
|--|---------------------------------------------|
|  |                                             |
|  | - 3 0 0 . 0    5 0 0                        |
|  | 4 4 0 C                                     |
|  | HRC60 HRC62                                 |
|  | 1 0    1 3    1 5    2 0    3 0    4 0 mm   |
|  | 4 0 mm ( N )                                |
|  | 7 8 * 1 3 8 mm    9 0 * 1 3 8 mm    L * * H |
|  | 3 0 0 W    2 2 0 V / 1 1 0 V                |
|  | 9 k g                                       |

| [ M p a | 5 0     | 1 0 0   | 3 0 0   | 4 0 0   | 6 0 0   | 8 0 0   | 1 0 0 0 | 1 2 0 0 | 1 5 0 0 |
|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 8 T     | 0 . 2 5 | 0 . 5   | 1 . 5   | 2 . 0 1 | 3 . 0 1 | 4 . 0 2 | 5 . 0 2 | 6 . 0 3 | 7 . 5 3 |
| 1 0 T   | 0 . 3 9 | 0 . 7 8 | 2 . 3 5 | 3 . 1 4 | 4 . 7 1 | 6 . 2 8 | 7 . 8 5 | 9 . 4 2 | 1 1 . 7 |
| 1 2 T   | 0 . 5 6 | 1 . 1 3 | 3 . 3 9 | 4 . 5 2 | 6 . 7 8 | 9 . 0 4 | 1 1 . 3 | 1 3 . 5 | 1 6 . 9 |
| 1 3 T   | 0 . 6 6 | 1 . 3 2 | 3 . 9 8 | 5 . 3   | 7 . 9 6 | 1 0 . 6 | 1 3 . 2 | 1 5 . 9 | 1 9 . 9 |
| 1 5 T   | 0 . 8 8 | 1 . 7 6 | 5 . 3   | 7 . 0 6 | 1 0 . 6 | 1 4 . 1 | 1 7 . 6 | 2 1 . 2 | 2 6 . 5 |
| 2 0 T   | 1 . 5 7 | 3 . 1 4 | 9 . 4 2 | 1 2 . 5 | 1 8 . 8 | 2 5 . 1 | 3 1 . 4 | 3 7 . 6 | 4 7 . 1 |

: PMHD



P I D

|  |                  |                           |
|--|------------------|---------------------------|
|  | PMHD - A         | PMHD - B                  |
|  | 0 . 0 - 300 . 0  | 0 . 0 - 300 . 0           |
|  | Cr 12MoV         | Cr 12MoV                  |
|  | 50mm ( d )       | 25mm ( d )                |
|  | 15 - 100 m       | 25 50 100 250 500 m ( 6 ) |
|  | 200 * 60mm D * H | 200 * 60mm ( D * H )      |
|  | 220V / 300W      | 220V / 300W               |
|  |                  |                           |



K i n t e k   P r e s s

W h a t s A p p