



K I N T E K P R E S S

C o n t a c t u s f o r m o r e c a t a l o g s o f

KINTEK PRESS

> > >

KINTEK

Press



2 T K B r F t i r

: K T - K B P



KINTEK
2 T
K B r
F T I R

	PCKBR - 2 T
(T)	0 - 2 (3 0 M p a)
	4 5 m m
	1 M P a / 1 0 m i n
	4 5 m m
	2
W × D	5 4 × 5 5 m m
W × L × H	1 0 0 × 2 2 0 × 2 2 0 m m
k g	4 . 8 k g

: PCMP



K I N T E K

	PCMP - 2 T	PCMP - 5 T	PCMP - 12 T	PCMP - 15 T	PCMP - 24 T	PCMP - 30 T	PCMP - 40 T
	0 - 2 T (25MPa)	0 - 5 T (0 - 31 . 4 MPa)	0 - 12 T (0 - 30 MPa)	0 - 15 T (0 - 30 MPa)	0 - 24 T (0 - 34 MPa)	0 - 30 T (0 - 31 . 0 MPa)	0 - 40 T (0 - 30 MPa)
	32 mm (d)	45 mm (d)	70 mm (d)	80 mm (d)	95 mm (d)	110 mm (d)	130 mm (d)
T	30 mm	30 mm	30 mm	30 mm	30 mm	40 mm	50 mm
	1 MPa / 10 min	1 MPa / 10 min	1 MPa / 10 min	1 MPa / 10	1 MPa / 10	1 MPa / 10	1 MPa / 10
	50 mm (D)	80 mm (D)	80 mm (D)	90 mm (D)	105 mm (D)	120 mm (D)	140 mm (D)
	2	2	2	2			
	85 × 120 mm (M × H)	96 × 130 mm (M × H)	96 × 130 mm (M × H)	140 × 150 mm (M × H)	80 × 150 mm (M × H)	92 × 160 mm (M × H)	106 × 185 mm (M × N)
	210 × 150 × 350 mm (L × W × H)	225 × 155 × 380 mm (L × W × H)	225 × 155 × 380 mm (L × W × H)	245 × 175 × 390 mm (L × W × H)	245 × 175 × 415 mm (L × W × H)	275 × 195 × 420 mm (L × W × H)	295 × 215 × 500 mm (L × W × H)
	12 Kg	28 Kg	28 Kg	38 Kg	42 Kg	56	75 Kg

: P C F



K I N T E K

	PCF - 15 T	PCF - 24 T	PCF - 30 T	PCF - 40 T	PCF - 60 T
	0 - 15 T (0 - 30 MPa)	0 - 24 T (0 - 34 MPa)	0 - 30 T (0 - 31.5 MPa)	0 - 40 T (0 - 30 MPa)	0 - 60 T (0 - 34 MPa)
	80 mm (d)	95 mm (d)	110 mm (d)	130 mm (d)	150 mm (d)
(T)	30 mm	30 mm	40 mm	50 mm	50 mm
	1 MPa / 10 min	1 MPa / 10	1 MPa / 10	1 MPa / 10	1 MPa / 10
	90 mm (D)	105 mm (D)	120 mm (D)	140 mm (D)	160 mm (D)
	4	4	4	4	4
	80 × 130 mm (M × N)	112 × 160 mm (M × N)	112 × 160 mm (M × N)	126 × 185 mm (M × N)	185 × 250 mm (M × N)
	260 × 175 × 395 mm ()	305 × 195 × 425 mm (H)	305 × 195 × 425 mm (H)	355 × 215 × 505 mm (H)	405 × 240 × 565 mm (L × W × H)
	42 Kg	65 Kg	65 Kg	90 Kg	120 Kg

	MPa
1	0.75
3	2.2
5	3.7
10	7.5
12	9
15	11.3
20	15
30	22.5

4 0

3 0

3 5 MPa

: P T 1 0



	P T 1 0
	3 C r 1 3
	1 0 1 2 1 4 1 5 1 6 1 8 1 9 (d)
	1 2 0 * 2 0 0 * 2 8 0 mm L * W * H
	1 0 k g

: P C 2 N S



K I N T E K
R 4 4

C R 2 0 3 2

	P C 2 N S
	0 - 2 T (0 - 25MPa)
	3 2mm (d)
	0 . 0 0 - 4 0 . 0 0MPa
	C R 2 0
	C R 1 6 C R 2 0 C R 2 4 C R 3 0
	0 . 8 1 . 2
	C R 1 6 C R 2 0 C R 2 4 C R 3 0
	0 . 4
	2 1 0 * 1 6 5 * 2 9 0mm (L X * W * H)
	1 2 K g

: P C 2 N



CR 2 0 3 2 L R 4 4

	P C - 2 N
	0 - 2 T (0 - 25 MP a)
	3 2 mm (d)
	CR 2 0
	CR 16 CR 20 CR 24 CR 30
	0 . 8 1 . 2
	CR 16 CR 20 CR 24 CR 30
	0 . 4
	2 1 0 * 1 6 5 * 2 9 0 mm (L X * W * H)
	1 2 K g

: P C B P



K I N T E K

	PCBP - 2 T ()		PCBP - 1 . 5 T
	0 - 2 T (0 - 25MPa)		50 - 1500 kg
	32mm (d)		- -
			0 999
	CR20	LCD	4 . 3 LCD
	CR16 , CR20 , CR24 , CR30 optio		CR16 , CR20 , CR24 , CR30
	0 . 8 1 . 2		CR16 CR20 CR24 CR30
	CR16 , CR20 , CR24		CR20
			220x240x380 (L X W X H)
	210×165×290mm (L×W×H)		220V (50Hz / 60Hz)
	12 Kg		35 Kg

: PCEA



KINTEK

	PCEA - 12 T	PCEA - 20 T	PCEA - 30 T	PCEA - 40 T	PCEA - 60 T	PCEA - 100 T	PCEA - 150 T
	0.2 - 12.0	1 20.0	1 30.0	1 40.0	1 60.0	1 - 100.0	1 - 150.0
	4.3	LCD			7	LCD	
	10						
(T)	30 mm			50 mm			
(M × N)	110 × 140 mm	140 × 160 mm	140 × 160 mm	175 × 180 mm	185 × 220 mm	185 × 250 mm	200 × 260 mm
L × W × H	185 × 320 × 360 mm	230 × 390 × 4 mm	230 × 390 × 4 mm	280 × 460 × 5 mm	300 × 520 × 5 mm	330 × 580 × 6 mm	400 × 620 × 620 mm
	240W (220V / 110V)	550W (220V / 110V)				1500W 220V / 110V	
	50 Kg	90 Kg		150 Kg	180 Kg	240 Kg	380 Kg

: P C E S



K I N T E K

	PCES - 40T	PCES - 65T	PCES - 100T	PCES - 150T	PCES - 200T
	0 - 40	0 - 65	1 - 100	1 - 150	1 - 200
	130mm (d)	160mm (d)	200mm (d)	250mm (d)	290mm (d)
	7 LCD	7 LCD	7 LCD	7 LCD	7 LCD
(T)	50mm	50mm	50mm	50mm	50mm
	160×300mm (M×N)	220×300mm (M×N)	260×250mm (M×N)	285×290mm (M×N)	290×300mm (M×N)
	500×700×800mm (L×W×H)	580×700×800mm (L×W×H)	850×500×950mm (L×W×H)	950×600×1000mm (L×W×H)	1000×650×1050mm (L×W×H)
	1500w (220v / 110v)	1500w (220v / 110v)	1500 (220V / 110V)	1500W (220V / 110V)	1500W (220V / 110V)
	200kg	280kg	520kg	620kg	850kg

X r f K b r F t i r

: P C P E



K I N T E K

	PCPE - 20 T	PCPE - 30 T	PCPE - 40 T	PCPE - 60 T
	0 - 20 T (0 - 28 MP a)	0 - 30 T (0 - 31.5 MP a)	0 - 40 T (0 - 30 MP a)	0 - 60 T (0 - 33 MP a)
	95 mm (d)	110 mm (d)	130 mm (d)	150 mm (d)
	0.00 - 40.00 MP a	0.00 - 40.00 MP a	0.00 - 40.00 MP a	0.00 - 40.00 MP a
(T)	30 mm	40 mm	50 mm	50 mm
	1 MP a / 10 m i n	1 MP a / 10 m i n	1 MP a / 10 m i n	1 MP a / 10
	/	/	/	/
	/	/	/	/
	105 mm (D)	120 mm D	140 mm (D)	160 mm D
	4	4	4	4
	80 × 150 mm (M × N)	92 × 160 mm (M × N)	115 × 185 mm (M × N)	185 × 250 mm (M × N)
	245 × 415 × 415 mm (× ×)	275 × 430 × 420 mm (× ×)	295 × 450 × 500 mm (× ×)	405 × 470 × 565 mm (L × W × H)
	220 V (50 Hz / 60 Hz)	220 V (50 Hz / 60 H)	220 V (50 Hz / 60 H)	220 V (50 Hz / 60 Hz)
	58 Kg	72 Kg	92 Kg	140 Kg

1 [	1.41 [MP a
2 [	2.82 [MP a
3	4.23 MP a
5 [	7.06 MP a

8	11.3 [MPa
10 [	14.1 MPa
12	17 [MPa
15	22.6 MPa
20	28 [MPa
35MPa	

: P P 2 N



K I N T E K

-

3 0 0 6 0 0

	P P 2 N		
	5 0 - 1 5 0 0 k g		
	-		
	0 - 9 9 9		
L C D	4 . 3	L C D	
	C R 1 6 C R 2 0 C R 2 4 C R 3 0		
	C R 1 6 C R 2 0 C R 2 4 C R 3 0		
	C R 2 0		
	2 2 0 * 2 4 0 * 3 8 0 (l * w * h)		
	2 2 0 V (5 0 H z / 6 0 H z)		
	3 5 k g		

X r f K b r

: P M X A



K i n T e k
X R F

X R F / I R

	P M X A - 3 0 T	P M X A - 4 0 T	P M X A - 6 0 T
	1 3 0 . 0	0 4 0 . 0	0 6 0 . 0
	- - -	- - -	- - -
	0 9 9 9	0 9 9 9	0 - 9 9 9
	4 . 3	4 . 3	4 . 3
	1 0	1 0	1 0
	/ / 1	/ / 1	/ / 1
	4 0 mm	4 0 mm	4 0 mm
	4 4 0 C	4 4 0 C	4 4 0 C
L × W × H	2 5 0 × 3 9 0 × 4 6 0 mm	2 8 0 × 4 6 0 × 5 5 0 mm	3 0 0 × 5 2 0 × 5 8 0 mm
	5 5 0 W 2 2 0 V / 1 1 0 V	5 5 0 W 2 2 0 V / 1 1 0 V	5 5 0 W 2 2 0 V / 1 1 0 V
	1 2 0 K g	1 5 0 K g	1 8 0 K g

: P C G



	PCG - 25T1818	PCG - 25T2020
	0 - 25 T	0 - 25 T
	-	-
	0 999 . 59	0 999 . 59
	500	500
	180×180mm	200×200mm
	304	304
	780×650×700mm	780×650×700mm
	240×260mm	240×260mm
	- 0 . 1MPa	- 0 . 1MPa
	1200×950×1800mm (L×W×H)	1200×950×1800mm (L×W×H)
	220V 50Hz	220V 50Hz



K i n t e k P r e s s

W h a t s A p p