

24 T 30 T 60 T

: PCH



	PCH - 24T1010	PCH - 30T2020	PCH - 30T1818
	0 24 . 0	0 30 . 0	0 30 . 0
	95mm (d)	110mm (d)	150mm (d)
	- 300 . 0 / 500 . 0	- 300 . 0 / 500 . 0	- 300 . 0 / 500 . 0
	[	[	[
	100×100mm M×N	200×200mm (M×N)	180×180mm (M×N)
	245×175×500mm (K×P×H)	405×260×525mm (K×P×H)	405×260×525mm (K×P×H)
	500×175×500mm (L×W×H)	950×260×525mm (L×W×H)	950×260×525mm (L×W×H)
	600 W (220V / 110V)	1200 W (220V / 110V)	1000W (220V / 110V)
	60 Kg	180 Kg	180 Kg