

: PCSE



KINTEK

300

| | PCSE - 40T4040 | PCSE - 30T3030 |
|--|-----------------------|-----------------------|
| | 0 - 40.0 | 0 - 30.0 |
| | - | - |
| | - 300.0 | - 300.0 / 500.0 |
| | | |
| | [| |
| | 400×400mm (M×N) | 300×300mm (M×N) |
| | 500×480×650mm (K×P×H) | 380×350×600mm (K×P×H) |
| | 850×480×650mm (L×W×H) | 700×400×600mm (L×W×H) |
| | 5500W (220V/110V) | 3500W 220V/110V |
| | 480 Kg | 280 Kg |