

: PCAH



K I N T E K

	PCAH - 25T1818 / 1818G	PCAH - 25T2020 / G	PCAH - 30T3030 / 3030G	PCAH - 40T4040 / 4040G
	0 25 . 0	0 25 . 0	0 30 . 0	0 40 . 0
	- -	- -	- -	- -
	- 300 . 0 / 500 . 0	- 300 . 0 / 500 . 0	- 300 . 0 / 500 . 0	- 300 . 0
	[	[	[	[
	180 × 180mm (M × N)	200 × 200mm (M × N)	300 × 300mm (M × N)	400 × 400mm (M × N)
	300 × 390 × 560mm (L × W × H)	300 × 390 × 560mm (L × W × H)	400 × 490 × 580mm (L × W × H)	500 × 550 × 620mm (L × W × H)
	1700 W (220V / 110V)	1700W (220V / 110V)	3500W (220V / 110V)	5500 W (220V / 110V)
	140 Kg	140 Kg	280 Kg	480 Kg