

C i p

: P C I A



(C I P)

K I N T E K

	P C I A - 20 T	P C I A - 40 T	P C I A - 60 T	P C I A - 100 T
	110 mm (d)	130 mm (d)	150 mm (d)	200 mm (d)
	-	-	-	-
	4 . 3 L C D	4 . 3 L C D	4 . 3 L C D	7 L C D
	300 - 500 MPA	300 - 500 MPA	300 - 500 MPA	300 - 500 MPA
	30 × 150 mm (M × N)	40 × 150 mm (M × N)	50 × 150 mm / 30 × 150 mm	60 × 150 (M × N)
(T)	50 mm	50 mm	50 mm	50 mm
	240 × 390 × 560 × ×	280 × 460 × 660 × ×	/	330 × 580 × 720 × ×
	550 W (220 V / 110	550 W (220 V / 110	550 W (220 V / 110	550 W (220 V / 110
			)	)
	120 KG	180 KG	240 KG	290 KG