

C i p

: P C E S I



K I N T E K L a b

	P C E S I - 65 T	P C E S I - 100 T	P C E S I - 150 T	P C E S I - 200 T
	0 - 65 T	0 - 100 T	0 - 150 T	0 - 200 T
	160 mm (d)	200 mm (d)	200 mm (d)	290 mm (d)
	-	-	-	-
	7" LCD			
	0 - 300 MPa	0 - 300 MPa	0 - 300 MPa	0 - 300 MPa
	€ 50 × 150 mm (M × N)	€ 60 × 150 mm (M × N)	€ 80 × 150 mm (M × N)	€ 90 × 150 mm (M × N)
(T)	50 mm	50 mm	50 mm	50 mm
	220 × 400 mm (M × N)	260 × 400 mm (M × N)	280 × 400 mm (M × N)	290 × 420 mm (M × N)
	700 × 450 × 1050 mm (L × W × H)	850 × 500 × 1100 mm (L × W × H)	950 × 550 × 1150 mm (L × W × H)	1000 × 650 × 1200 mm (L × W × H)
	1500 W 220 V / 110 V			
	350 kg	580 kg	680 kg	980 kg