

X r f K b r F t i r

: P C P E



K I N T E K

	PCPE - 20 T	PCPE - 30 T	PCPE - 40 T	PCPE - 60 T
	0 - 20 T (0 - 28 MP a)	0 - 30 T (0 - 31.5 MP a)	0 - 40 T (0 - 30 MP a)	0 - 60 T (0 - 33 MP a)
	95 mm (d)	110 mm (d)	130 mm (d)	150 mm (d)
	0.00 - 40.00 MP a	0.00 - 40.00 MP a	0.00 - 40.00 MP a	0.00 - 40.00 MP a
(T)	30 mm	40 mm	50 mm	50 mm
	1 MP a / 10 min	1 MP a / 10 min	1 MP a / 10 min	1 MP a / 10
	/	/	/	/
	/	/	/	/
	105 mm (D)	120 mm D	140 mm (D)	160 mm D
	4	4	4	4
	80 × 150 mm (M × N)	92 × 160 mm (M × N)	115 × 185 mm (M × N)	185 × 250 mm (M × N)
	245 × 415 × 415 mm (× ×)	275 × 430 × 420 mm (× × × H)	295 × 450 × 500 mm (× × × H)	405 × 470 × 565 mm (L × W × H)
	220 V (50 Hz / 60 Hz)	220 V (50 Hz / 60 H)	220 V (50 Hz / 60 H)	220 V (50 Hz / 60 Hz)
	58 Kg	72 Kg	92 Kg	140 Kg

1 [	1.41 [MP a
2 [	2.82 [MP a
3	4.23 MP a
5 [	7.06 MP a

8	11.3 [MPa]
10 [	14.1 MPa
12	17 [MPa]
15	22.6 MPa
20	28 [MPa]
35MPa	