

: PCBP



KINTEK

	PCBP- 2T ( )		PCBP- 1.5T
	0- 2T ( 0- 25 MP a)		50- 1500kg
	32mm ( d)		- -
			0 999
	CR20	LCD	4.3 LCD
	CR16, CR20, CR24, CR30optio		CR16, CR20, CR24, CR30
	0.8 1.2		CR16 CR20 CR24 CR30
	CR16, CR20, CR24		CR20
			220x240x380(L X W X H)
	210x165x290mm(L x W x H)		220V( 50Hz / 60Hz)
	12Kg		3.5Kg