

: PCG



|  | PCG - 25T1818           | PCG - 25T2020           |
|--|-------------------------|-------------------------|
|  | 0 - 25 T                | 0 - 25 T                |
|  | -                       | -                       |
|  | 0 999 . 59              | 0 999 . 59              |
|  | 500                     | 500                     |
|  | 180×180mm               | 200×200mm               |
|  | 304                     | 304                     |
|  | 780×650×700mm           | 780×650×700mm           |
|  | 240×260mm               | 240×260mm               |
|  | - 0 . 1MPa              | - 0 . 1MPa              |
|  | 1200×950×1800mm (L×W×H) | 1200×950×1800mm (L×W×H) |
|  | 220V 50Hz               | 220V 50Hz               |