

: P C S M



K I N T E K

-

	PCSM - 30T3030	PCSM - 40T4040
	0 30 . 0	0 40 . 0
	130mm (d)	130mm (d)
	- 300 . 0 / 500 . 0	- 300 . 0
	[	
	300×300mm (M×N)	400×400mm (M×N)
	380×350×600mm (K×P×H)	500×480×650 (K×P×H)
	700×400×600mm (L×W×H)	800×480×650 (L×W×H)
	3000W (220V / 110V)	5000W (220V / 110V)
	260Kg	460Kg