

: PCY



K I N T E K

	PCY - 5T1212	PCY - 10T1818	PCY - 10T2020	PCY - 15T3030
	0 - 5.0	0 10.0	0 10.0	0 15.0
	50mm (d)	65mm (d)	65mm (d)	95mm d
	- 300.0 / 500.0	- 300.0 / 500.0	- 300.0 / 500.0	- 300.0 / 500.0
	[	[	[	[
	120×120mm( M×N)	180×180mm( M×N)	200×200mm( M×N)	300×300mm( M×N)
	140×140×60mm	180×180×60mm	200×200×60mm	300×300×65mm
	250×230×390mm( L×W×H)	290×290×420mm( L×W×H)	320×290×420mm( L×W×H)	450×420×450mm( L×W×H)
	700W( 220V / 110V)	1000W( 220V / 110V )	1200W( 220V / 110V)	3000W( 220V / 110V )
	55 Kg	90Kg	95Kg	180Kg