

: PCMP



K I N T E K

	PCMP - 2 T	PCMP - 5 T	PCMP - 12 T	PCMP - 15 T	PCMP - 24 T	PCMP - 30 T	PCMP - 40 T
	0 - 2 T (25MPa)	0 - 5 T (0 - 31 . 4 MPa)	0 - 12 T (0 - 30 MPa)	0 - 15 T (0 - 30 MPa)	0 - 24 T (0 - 34 MPa)	0 - 30 T (0 - 31 . 0 MPa)	0 - 40 T (0 - 30 MPa)
	32 mm (d)	45 mm (d)	70 mm (d)	80 mm (d)	95 mm (d)	110 mm (d)	130 mm (d)
T	30 mm	30 mm	30 mm	30 mm	30 mm	40 mm	50 mm
	1 MPa / 10 min	1 MPa / 10 min	1 MPa / 10 min	1 MPa / 10	1 MPa / 10	1 MPa / 10	1 MPa / 10
	50 mm (D)	80 mm (D)	80 mm (D)	90 mm (D)	105 mm (D)	120 mm (D)	140 mm (D)
	2	2	2	2			
	85 × 120 mm (M × H)	96 × 130 mm (M × H)	96 × 130 mm (M × H)	140 × 150 mm (M × H)	80 × 150 mm (M × H)	92 × 160 mm (M × H)	106 × 185 mm (M × N)
	210 × 150 × 350 mm (L × W × H)	225 × 155 × 380 mm (L × W × H)	225 × 155 × 380 mm (L × W × H)	245 × 175 × 390 mm (L × W × H)	245 × 175 × 415 mm (L × W × H)	275 × 195 × 420 mm (L × W × H)	295 × 215 × 500 mm (L × W × H)
	12 Kg	28 Kg	28 Kg	38 Kg	42 Kg	56	75 Kg