

: P C F



K I N T E K

|     | PCF - 15T             | PCF - 24T             | PCF - 30T             | PCF - 40T             | PCF - 60T                     |
|-----|-----------------------|-----------------------|-----------------------|-----------------------|-------------------------------|
|     | 0 - 15T (0 - 30MPa)   | 0 - 24T (0 - 34MPa)   | 0 - 30T (0 - 31.5MPa) | 0 - 40T (0 - 30MPa)   | 0 - 60T (0 - 34MPa)           |
|     | 80mm (d)              | 95mm (d)              | 110mm (d)             | 130mm (d)             | 150mm (d)                     |
|     |                       |                       |                       |                       |                               |
| (T) | 30mm                  | 30mm                  | 40mm                  | 50mm                  | 50mm                          |
|     |                       |                       |                       |                       |                               |
|     | 1MPa / 10min          | 1MPa / 10             | 1MPa / 10             | 1MPa / 10             | 1MPa / 10                     |
|     | 90mm (D)              | 105mm (D)             | 120mm (D)             | 140mm (D)             | 160mm (D)                     |
|     | 4                     | 4                     | 4                     | 4                     | 4                             |
|     | 80 × 130mm (M × N)    | 112 × 160mm (M × N)   | 112 × 160mm (M × N)   | 126 × 185mm (M × N)   | 185 × 250mm (M × N)           |
|     | 260 × 175 × 395mm (H) | 305 × 195 × 425mm (H) | 305 × 195 × 425mm (H) | 355 × 215 × 505mm (H) | 405 × 240 × 565mm (L × W × H) |
|     | 42Kg                  | 65Kg                  | 65Kg                  | 90Kg                  | 120Kg                         |

|    | MPa  |
|----|------|
| 1  | 0.75 |
| 3  | 2.2  |
| 5  | 3.7  |
| 10 | 7.5  |
| 12 | 9    |
| 15 | 11.3 |
| 20 | 15   |
| 30 | 22.5 |

4 0

3 0

3 5 MPa